



12W

VT-759-12 12W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000k WHITE SQUARE

Lumens 1100	Beam Angle 120	Dimensions 100x100x100mm
-----------------------	--------------------------	------------------------------------

Day White
 SKU:8528



Technical Information

Watts:	12	LED Chip Type:	SMD
Lumens:	1100	IP Rating:	IP65
Shape:	Square	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	120	PF:	>0.45
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Input Power:	AC:220-240V,50/60Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes

Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.7
Unit CBM	0.001331

Listing Details

EAN Code	3800157638623
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1000

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES