

## **Product Specification Sheet**

	12W VT-828 12W LED WALL LIGHT COLORCODE:3000K,BLACK -ROUND					
	Lumens 900	Beam Angle 158	Dimensior 169x100	-		
	Warm White SKU:8541		<b>2</b> Y E A R S WARRANTY	SENSOR Compatible	SAVE LET TO 80% ENERCY	

## **Technical Information**

Output Voltage:	DC:36-40V
Watts:	12
Lumens:	900
Shape:	Round
eam Angle:	158
utput Current:	280mA
o. Of Led:	72
nit Color:	Black
Body Type:	PC
Long life:	20,000 Hours

## Features

- Modern Wall lights available in sleek and stylish designs.
- Excellent heat dissipation
- Available in different color options - Warm White and Day White
  - Easy installation and Maintenance
    - Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

Unit Details		Listing Details	
Gross Weight(GW) Kgs	0.528	EAN Code	3800157638906
Unit CBM	0.00289	Commodity Code	9405403990
Master Box Packaging			
Master Box Qty (Pcs Per Carton)	20		
Qty Per Pallet	400		

