


# **Product Specification Sheet**



### 4W

VT-834 4W LED WALL LIGHT(ROUND) COLORCODE:3000K IP65-BLACK BODY

Lumens 440

Beam Angle

Dimensions Ø112mm

Warm White SKU:8553







## **Technical Information**

Watts:	4
Lumens:	440
Shape:	Round
Beam Angle:	90
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

 IP Rating:
 IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.45

 CRI:
 >80

 Operation Temperature:
 -20 to +45°c

 Input Power:
 AC:220-240V,50/60Hz

 Sensor Compatibility:
 Yes

## **Features**

Ž,

Perfect choice for Interior and Exterior aesthetics

Wall washer to create attractive beam designs

High quality LED Chips for reliable lighting effect

IP65 rated solid ingress protection

Glass screen for controlled light beams

Available in different color options - Warm White and Day White

Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

#### **Unit Details**

 Gross Weight(GW) Kgs
 0.63

 Unit CBM
 0.00164

## Master Box Packaging

Master Box Qty (Pcs Per Carton)

## **Listing Details**

EAN Code 3800157640473

Commodity Code 9405403990



20

OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES