


Product Specification Sheet



Technical Information

Watts:	4
Lumens:	440
Shape:	Round
Beam Angle:	90
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

Features

- Perfect choice for Interior and Exterior aesthetics
- Wall washer to create attractive beam designs
- >>>>>> High quality LED Chips for reliable lighting effect
 - IP65 rated solid ingress protection
 - Glass screen for controlled light beams
 - Available in different color options Warm White and Day White
 - Applications Outdoor, Façade, Residential, Restaurants, Building and many more

24Ĥ) Note:

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details		Listing Details			
Gross Weight(GW) Kgs	0.63	EAN Code	3800157640480		
Unit CBM	0.00164	Commodity Code	9405403990		
Master Box Packaging					
Master Box Qty (Pcs Per Carton)	20				
READY STOCKS IN UK & EU Www.vtacexports.com					