

Product Specification Sheet



4W VT-844 4W LED WALL LIGHT COLORCODE:3000K-WHITE

Lumens 150

Beam Angle 41

Dimensions 83x123x30mm

Warm White SKU:8560







Technical Information

Watts:	4
Lumens:	150
Shape:	Rectangle
On/Off Cycles:	>15000
Beam Angle:	41
Unit Color:	White
Body Type:	Nylon
Long life:	20,000 Hours
LED Chip Type:	SMD

 IP Rating:
 IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.4

 CRI:
 >80

 Operation Temperature:
 -20°C to +45°C

 Input Power:
 AC:220-240V,50/60Hz

 Sensor Compatibility:
 Yes

Features



Modern Wall lights available in sleek and stylish designs.

Excellent heat dissipation

Available in different color options - Warm White and Day White

Easy installation and Maintenance

Application: Perfect for halls, pathways, Bedroom, Kitchen etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

 Gross Weight(GW) Kgs
 0.226

 Unit CBM
 0.00061

Master Box Packaging

Master Box Qty (Pcs Per Carton)

Listing Details

EAN Code 3800157643719

COUNTRIES

Commodity Code 9405403990



50