

# **Product Specification Sheet**



#### 4W VT-844 4W LED WALL LIGHT COLORCODE:3000K-BLACK

Lumens 150

Beam Angle 41

Dimensions 83x123x30mm

Warm White SKU:8561







### **Technical Information**

Watts:	4
Lumens:	150
Shape:	Rectangle
On/Off Cycles:	>15000
Beam Angle:	41
Unit Color:	Black
Body Type:	Nylon
Long life:	20,000 Hours
LED Chip Type:	SMD

 IP Rating:
 IP65

 Dimmable:
 No

 Warranty (Years):
 2

 PF:
 >0.4

 CRI:
 >80

 Operation Temperature:
 -20°C to +45°C

 Input Power:
 AC:220-240V,50/60Hz

 Sensor Compatibility:
 Yes

#### **Features**

✓ Moder

Modern Wall lights available in sleek and stylish designs.



Available in different color options - Warm White and Day White

Easy installation and Maintenance

Application: Perfect for halls, pathways, Bedroom, Kitchen etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

**Unit Details** 

 Gross Weight(GW) Kgs
 0.226

 Unit CBM
 0.000613

50

Master Box Packaging

Master Box Qty (Pcs Per Carton)

#### Listing Details

EAN Code 3800157643726

Commodity Code 9405403990

