



**18W**

VT-1881G SQ 18W GLASS LED PANELS COLORCODE:4000K SQUARE

Lumens  
**1260**

Beam Angle  
**120**

Dimensions  
**198x198x40mm**

Day White  
SKU:6280

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start: 0-100% in 1s

Watts: 18

Lumens: 1260

Shape: Square

Beam Angle: 120

Cutting Size: 145x145mm

Unit Color: TRANSPARENT

Body Type: Aluminium + Glass

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

PF: >0.9

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:100-240V,50/60Hz

Sensor Compatibility: Yes

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in less than 1s
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

|                      |         |
|----------------------|---------|
| Gross Weight(GW) Kgs | 0.925   |
| Length(Box)mm        | 300     |
| Width(Box)mm         | 70      |
| Height(Box)mm        | 220     |
| Unit CBM             | 0.00396 |

### Listing Details

|                |               |
|----------------|---------------|
| EAN Code       | 3800157615785 |
| Commodity Code | 9405403990    |

### Master Box Packaging

|                                 |     |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 20  |
| Qty Per Pallet                  | 320 |

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES