

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200900037

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Receptacle, 5 Poles, M8 x 0.5 Mounting Threads, Female (Straight) to 22 AWG Leads, 0.30m (11.81") Length



Series image - Reference only

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Receptacles
Series	120090
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	78678833576
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	None
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Net Weight	10.284/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	24
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	4R5P00A27C300
Reference - Drawing Numbers	
Sales Drawing	1200908076-000, SD-120090-009

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - ED/71/2019 (16 July 2019)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120090 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION