

LD70 Laser Distance Meter

Designed for one-person operation to measure distances from 2 inches to 230 feet (0.05 to 70m) in seconds with high accuracy and repeatability

Features:

- Measures from 2 inches to 230 feet (0.05 to 70m)
- Addition/Subtraction/Area/Volume measurement
- Indirect measurement using Pythagorean theorem
- Stakeout function for stud or fence layout
- Continuous real-time on-screen angle display
- Memory stores 20 readings
- Selectable front/back reference edge
- Included 4" x 2" reflective plate for better response and accuracy at longer distances

Applications:

- New construction
- Home Inspection
- Floor and Carpet Installation
- Electrical, Cable, Alarm and Telecomm wiring
- Painting
- Landscaping and Fence installation
- HVAC and Heating



	LD70
Measurement Range	2 inches to 230 feet (0.05 to 70m)
Measurement Accuracy	±0.19" (±3mm)
Addition/Subtraction/Area/Volume	•
Continuous Measurement	•
Real-Time On-Screen Angle Display	•
Stakeout Function	•
Indirect Measurement with Pythagorean	•
Historical Records	20 readings
Power	Two AAA batteries
Reference Edge	Selectable front/back
Dimensions	4.4 x 2 x 1.1" (112.3 x 51.6 x 28.8mm)
Weight	3.5oz (100g) without batteries

Ordering Information:

LD70 Laser Distance Meter (70m)