

8075 CamView IP Pro-X Security Camera Tester



The CamView IP Pro-X is designed for the installation and maintenance of analog SD, analog HD and network HD video surveillance systems

Features:

- Security Camera Tester with advanced cable & network capabilities
- Works with SD Analog, AHD 3.0, HD-CVI 3.0, HD-TVI 3.0, H.264, H.265 IP, NTSC/PAL, and all ONVIF enabled IP cameras
- USB, BNC, RJ45 and HDMI ports
- WiFi for connecting to WiFi cameras and to create a WiFi hotspot
- 25W PoE and 12VDC camera outputs
- Built-in DHCP server to set up IP cameras before the network is even wired
- RS485 PTZ Control
- Network Testing includes: Network Sniff, Subnet List and Ping Test
- TDR and RJ45 Cable Test
- Built-in Video Test Image Generator
- 7" touchscreen



Applications:

- One of the most advanced combined HD and IP camera testers on the market today for the security installer/technician to save time on the jobsite and have confidence that the installation is done right

IPC Protocol	ONVIF, RTSP, RTP
Ethernet Test	10/100M/1G detect; Loop detect; DHCP client & server; traffic detect; datalink quality detect
IPC Test	Discover the device, real time video, camera config, PTZ test, discover ONVIF device
WiFi Test	Support 2.4G & 5G; WiFi connection; WiFi list; Delay detection; packet loss rate test
Spectrum Test	Spatial frequency band signal scanning & detection; spatial noise signal detection
Poe Test power	PSE test -The tester supplies power (25W) / PD test-receives the power (802.3af/802.3at)
Analog Video Test	NTSC/PAL/HD-CVI 3.0/AHD 3.0/HD-TVI 3.0 Video In/Out BNCs; supports 8 level digital zoom
HDMI Signal Test	Can receive 720p, 1080p Can transmit various test images 720p & 1080p
12V Power Output	12V/2A output interface
TDR Test	Test network cable (4 pair) length; Max 427 to 656ft (130 to 200m); Accuracy 3.3ft (1m)
Coaxial PTZ Control Test	CVI protocol (Dahua); AHD protocol (Pelco c); TVI protocol (Hikvision)
485 PTZ test	More than 30 protocols
Display	7" TFT touchscreen , 1920 x 1200, 16.7M colors
Power	(2) Lithium-ion batteries; 10 hour work time
Dimensions/Weight	9.3 x 5.2 x 1.8" (236.5 x 133.4 x 45.4mm) / 2lbs (907g)

Ordering Information:

8075 CamView IP Pro-X 7" Ruggedized IP Security Camera Tester