

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0747521308](#)  
**Status:** **Active**  
**Overview:** SFP+ Passive Cable Assembly  
**Description:** SFP+-to-SFP+ Lite Passive Cable Assembly, 10Gbps, 30 AWG Cable, with Latch, 3.0m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR64395  
 UL E72548

**General**

Product Family Cable Assemblies  
 Series [74752](#)  
 Assembly Configuration Dual Ended Connectors  
 Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths., Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.  
 Connector to Connector SFP+-to-SFP+  
 Overview [SFP+ Passive Cable Assembly](#)  
 Product Name SFP Plus, SFP+  
 UPC 889056311700

**Physical**

Cable Length 3.0m  
 Circuits (Loaded) TWO DIFFERENTIAL PAIR  
 Gender Male-Male  
 Lock to Mating Part Yes  
 Net Weight 124.480/g  
 Number of Rows 2  
 Packaging Type Bag  
 Single Ended No  
 Wire Size AWG 30  
 Wire/Cable Type Twinax

**Electrical**

Impedance 100Ω  
 Shield Type Full Shield  
 Shielded Yes

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing 747520008-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ECHA\_01\_2020 (16 January 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[74752 Series](#)