


PRODUCT-DETAILS

SR2-SRN7520VK

ENCLOSURE GLASS DOOR 700X500X200 7035



General Information

Extended Product Type	SR2-SRN7520VK
Product ID	SRN7520VK
EAN	8015646753694
Catalog Description	ENCLOSURE GLASS DOOR 700X500X200 7035
Long Description	Enclosure with glazed door 700x500x200mm (HxWxD)

Ordering

EAN	8015646753694
Minimum Order Quantity	1 piece
Customs Tariff Number	85381000

Dimensions

Product Net Width	500 mm
Product Net Height	700 mm
Product Net Depth / Length	200 mm
Product Net Weight	16 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.515 m
Package Level 1 Height	0.225 m
Package Level 1 Depth / Length	0.720 m
Package Level 1 Gross Weight	16.500 kg
Package Level 1 EAN	8015646753694

Additional Information

Color	Grey
Construction Material	Galvanized steel
Cover Plate Type	Door
Degree of Protection	IP65
Housing Material	Steel
Interior Depth	183,5 mm
Mounting Type	Surface mounted (plaster)
Order Multiple	1 piece
Product Main Type	SR2 Enclosures
Product Name	Control and Automation Board
Protection Class	Grounded
Suitable for Product Class	SR2
Surface Finishing	Powder coating

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1STC804013D0203
Declaration of Conformity - CE	not applicable
Environmental Information	1STC804013D0203
Instructions and Manuals	1STM6041230001
RoHS Information	1STC860027

Classifications

ETIM 4	EC000200 - Enclosure for control circuit devices
ETIM 5	EC000200 - Enclosure for control circuit devices
ETIM 6	EC000058 - Empty cabinet
ETIM 7	EC000058 - Empty cabinet
Object Classification Code	U
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Enclosures → General Purpose Enclosures

