




**Product:** [RSF 30/13.5-01](#) 





7/8" Power Receptacle Connector: Male, front mount, 3-pin(2+PE), silver housing, 230 V AC/DC, 12 A, 0.75 mm<sup>2</sup>

### Product Description

7/8" Power Receptacle Connector: Male, front mount, 3-pin(2+PE), silver housing, 230 V AC/DC, 12 A, 0.75 mm<sup>2</sup>

### Technical Drawing



Typ/ type	Standard - Kontaktbelegung/ standard contact assignment	
	Polzahl/ number of poles	Farbkennung/ colour code
RSF 20/13.5..	2 	1 = braun / brown 2 = blau / blue
RSF 30/13.5..	3 	1 = braun / brown 2 = grün-gelb / gree-yellow 3 = blau / blue
RSF 40/13.5..	4 	1 = braun / brown 2 = weiß / white 3 = blau / blue 4 = schwarz / black
RSF 50/13.5..	5 	1 = schwarz / black 2 = blau / blue 3 = grün-gelb / green-yellow 4 = braun / brown 5 = weiß / white

### Technical Specifications

#### Technical Data

Product Family:	Power Connector
Product Sub Family:	7/8" Circular Connectors
Brand:	Lumberg Automation
Connector Type:	Receptacle
Type of Contact / Gender:	male
Connector Design:	Front mount

Number of Pins:	3(2+PE)
Shielding:	Unshielded
Rated Voltage:	250 V AC/DC
Operating Voltage:	230 V AC/DC
Rated Current:	12 A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10 <sup>9</sup> Ohm
Ambient Temperature (Operation):	-25 °C to +90 °C
Protection Degree / IP Rating:	IP68 (1h at 10 bar)
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)

## Materials

Contact Base Material:	CuZn
Contact Plating:	Cu/Au
Contact Bearer Material:	TPU
Contact Bearer Color:	orange
Housing Material:	CuZn, nickel-plated
O-Ring Material:	Neoprene

## Cable Data

Number of Wires:	3
Conductor material:	Cu
Wire Insulation Material:	PVC
Insulated Wire Diameter:	ø 2.40 mm
UL Cable Type:	AWM: 1569

## Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

## Notes

Protection Degree / IP Rating Note:	* only if mounted and locked in combination with Hirschmann / Lumberg connector.
Note Derating:	* Notice derating
Note:	Do not connect / disconnect under load.

## Variants

Item #	Item Description	Cable Length
11624	RSF 30/13,5-01	0.3 m

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.