

## Covering hood - EMG 22-H 7,5MM KLAR - 2946159


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design.  
Height: 7.5 mm, width: 22.5 mm



RoHS

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 10 pc   |
| Minimum order quantity               | 10 pc   |
| GTIN                                 | <br>4 017918 082116 |
| GTIN                                 | 4017918082116   |
| Weight per Piece (excluding packing) | 3.420 g   |
| Custom tariff number                 | 85472000  |
| Country of origin                    | Germany   |

### Technical data

#### General

|                  |                   |
|------------------|-------------------|
| Housing type     | Component housing |
| Housing material | Polycarbonate, PC |
| Color (RAL)      | transparent       |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

#### Dimensions

|        |         |
|--------|---------|
| Length | 38 mm   |
| Height | 7.5 mm  |
| Width  | 22.5 mm |
| Depth  | 75 mm   |

#### Technical data

|                     |   |
|---------------------|---|
| Number of positions | 8 |
|---------------------|---|

# Covering hood - EMG 22-H 7,5MM KLAR - 2946159

## Technical data

### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | V2 |
|--|----|

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27180400 |
| eCl@ss 4.1 | 27180400 |
| eCl@ss 5.0 | 27180500 |
| eCl@ss 5.1 | 27180500 |
| eCl@ss 6.0 | 27180800 |
| eCl@ss 7.0 | 27182702 |
| eCl@ss 8.0 | 27182702 |
| eCl@ss 9.0 | 27182702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC001031 |
| ETIM 6.0 | EC001031 |
| ETIM 7.0 | EC001031 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 31261501 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 31261501 |
| UNSPSC 18.0   | 31261501 |
| UNSPSC 19.0   | 31261501 |
| UNSPSC 20.0   | 31261501 |
| UNSPSC 21.0   | 31261501 |

## Approvals

### Approvals

## Covering hood - EMG 22-H 7,5MM KLAR - 2946159

### Approvals

Approvals


EAC

---

Ex Approvals

---

### Approval details

|     |   |         |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

---