

Locking - HSC-LR 9U KIT 2003 - 2201794

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DIN rail housing, 9U, Lock and Release system, width: 16.1 mm, height: 111.8 mm, depth: 8.8 mm, color: orange (2003)

Your advantages

- ✓ Tool-free mounting
- ✓ Push-in front connection technology
- ✓ Can be used for up to 42-pos. front connection technology

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 933599
GTIN	4046356933599
Weight per Piece (excluding packing)	5.850 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

Item properties

Brief article description	Locking
Type	HSC-LR 9U KIT 2003
Order No.	2201794
Housing type	DIN rail housing
Housing series	ME-IO
Type	9U
Mounting type	Snap in

Dimensions

Width [w]	16.1 mm
-------------	---------

Locking - HSC-LR 9U KIT 2003 - 2201794

Technical data

Dimensions

Height [h]	111.8 mm
Depth [d]	8.8 mm

Material data

Color (RAL)	orange (2003)
Flammability rating according to UL 94	V0
Housing material	Polyamide

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

PCB data

Mounting position	Vertical (horizontal DIN rail)
-------------------	--------------------------------

Packaging information

Pieces per package	10
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 4.0	EC001031
ETIM 5.0	EC002638
ETIM 6.0	EC002638

Locking - HSC-LR 9U KIT 2003 - 2201794

Classifications

ETIM

ETIM 7.0	EC002638
----------	----------

UNSPSC

UNSPSC 13.2	39121409
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

Approvals

Approvals




Approvals


UL Recognized / EAC



Ex Approvals



Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC		B.01742
-----	---	---------

Accessories

Accessories

Component housing upper part

Housing cover - ME-IO 18,8 C 5U 7035 - 2201803



DIN rail housing, 5U, Housing cover, width: 18.9 mm, height: 54.8 mm, color: light gray (7035)



Locking - HSC-LR 9U KIT 2003 - 2201794

Accessories

Housing cover - ME-IO 18,8 C 7U 7035 - 2201805



DIN rail housing, 7U, Housing cover, width: 18.9 mm, height: 76.8 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 3U S1 7035 - 2201801



DIN rail housing, 3U, Housing cover, width: 18.9 mm, height: 32.8 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 4U 7035 - 2201802



DIN rail housing, 4U, Housing cover, width: 18.9 mm, height: 43.8 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 6U 7035 - 2201804



DIN rail housing, 6U, Housing cover, width: 18.9 mm, height: 65.8 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 2U 7035 - 2201799



DIN rail housing, 2U, Housing cover, width: 18.9 mm, height: 21.8 mm, color: light gray (7035)

Locking - HSC-LR 9U KIT 2003 - 2201794

Accessories

Housing cover - ME-IO 18,8 C 3U 7035 - 2201800



DIN rail housing, 3U, Housing cover, width: 18.9 mm, height: 32.8 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 9U 7035 - 2201806



DIN rail housing, 9U, Housing cover, width: 18.9 mm, height: 98.8 mm, color: light gray (7035)

DIN rail connector

DIN rail bus connectors - ME 18,8 TBUS 1,5/5-ST-3,81KMGY - 2201813



DIN rail connector, number of positions: 5, pitch: 3.81 mm, color: light gray, contact surface: Gold, Articles with gold-plated contacts, bus connectors for connecting with electronic housings

Necessary add-on products

Feed-through header - HSCH 2,5-3U/12 9005 - 2201788



PCB headers, number of positions: 12, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering

Feed-through header - HSCH 2,5-2U/ 8 9005 - 2201789



PCB headers, number of positions: 8, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering, Please observe the derating curve of the item

Locking - HSC-LR 9U KIT 2003 - 2201794

Accessories

Feed-through header - HSCH 2,5-2U-TTTT 9005 - 2201790



PCB headers, number of positions: 4, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering,
Please observe the derating curve of the item

Feed-through header - HSCH 2,5-2U-2220 9005 - 2201792



PCB headers, number of positions: 6, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering,
Please observe the derating curve of the item
