

Junction box - E PE A 75X80X56 - 0899337

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Junction box, material: Polyester fiberglass reinforced, squirrell grey RAL 7000, 75 mm x 80 mm x 56 mm, type of locking: Screw-on cover

The figure shows a similar product



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626276069
Weight per Piece (excluding packing)	279.000 g
Custom tariff number	85389099
Country of origin	India
Note	Made to Order (non-returnable)

Technical data

General

Type	Empty enclosure with cover
Note	Prepared for direct installation of a DIN rail
Color	squirrell grey RAL 7000
Flammability rating according to UL 94	V0
Direct DIN rail mounting	yes
Useable DIN rail type	NS 15

Dimensions

Width	75 mm
Height	80 mm
Depth	56 mm
Clearance width, maximum DIN rail length	63 mm
Assembly length, max.	49 mm

Junction box - E PE A 75X80X56 - 0899337

Technical data

General

Housing material	Polyester fiberglass reinforced
Cover fastening	Screw-on cover
Note	Plus/minus screw
Fixing device	Integrated blind hole
	External fixing clips available as an option
Seal material	Chloroprene
Components	halogen-free

Ambient conditions

Degree of protection of housing (IP)	IP66
Protection class	II
Degree of protection (IK)	7.00 J EN 60079-0
Temperature in operating conditions	-40 °C ... 100 °C

Standards and Regulations

Standards/regulations	EN 60079-0
Flammability rating according to UL 94	V0


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings


Junction box - E PE A 75X80X56 - 0899337

Schematic diagram



Junction box - E PE A 75X80X56 - 0899337

Dimensional drawing



Junction box - E PE A 75X80X56 - 0899337

Classifications

eCl@ss

eCl@ss 10.0.1	27180190
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27180100
eCl@ss 6.0	27180100
eCl@ss 7.0	27180190
eCl@ss 8.0	27180190
eCl@ss 9.0	27180190

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000761
ETIM 5.0	EC000261
ETIM 6.0	EC000261
ETIM 7.0	EC000261

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	31261502
UNSPSC 18.0	31261502
UNSPSC 19.0	31261502
UNSPSC 20.0	31261502
UNSPSC 21.0	31261502

Accessories

Accessories

DIN rail

DIN rail, unperforated - NS 15 UNP AE EP 75X80 - 3002624



DIN rail, unperforated, width: 15 mm, height: 5.3 mm, material: Steel, galvanized, passivated with a thick layer, length: 63 mm, Suitable for PxC polyester terminal boxes, color: silver

Mounting material

Junction box - E PE A 75X80X56 - 0899337

Accessories

Fixing bracket - AE EMB EP 1 - 0899519



Fixing bracket, For polyester enclosure, color: silver

Mounting plate

Mounting plate - AE MP SH EP 75X80 - 0899429



Mounting plate, length: 2 mm, width: 64 mm, height: 69 mm, color: silver

Screwdriver tools

Screw insert - SF-BIT-PHSL 2-70 - 1212601



Screw bit, positive/negative PH/bladed, E6.3-1/4" drive, size: PH 2 x 70 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1174

Torque tool

Torque screwdriver - TSD-M 6NM - 1212226



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 3 - 6 Nm