

## Snap-in markers - UC-EM (20X7) - 0825499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 20 x 7 mm, Number of individual labels: 20

### Your advantages

- ✓ The UC-EM ... UniCard labeling range includes markers for devices and switching devices from a wide range of manufacturers
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 10 pc   |
| Minimum order quantity               | 10 pc   |
| GTIN                                 | <br>4 046356 364317 |
| GTIN                                 | 4046356364317   |
| Weight per Piece (excluding packing) | 8.810 g   |
| Custom tariff number                 | 39269097  |
| Country of origin                    | Poland  |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 7 mm  |
| Width (a)  | 20 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|            |                                |
|------------|--------------------------------|
| Color      | white                          |
| Components | free from silicone and halogen |

# Snap-in markers - UC-EM (20X7) - 0825499

## Technical data

### General

|   |                                     |
|---|-------------------------------------|
| Flammability rating according to UL 94                              | V2                                  |
| Material  | PA                                  |
| Wipe resistance   | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels   | 20                                  |
| Number of individual labels per row                                 | 5                                   |
| Printability  | Inkjet printing                     |
|   | Plotter                             |
| Device  | 5147888 BLUEMARK LED                |
|   | 5147999 BLUEMARK CLED               |
|   | 5144615 CMS-P1-PLOTTER              |
|   | 5146121 P1 UC-MAG 6                 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09             |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Alternating condensation climate with SO2 test specification        | following DIN 50018:2013-05         |
| Climate level   | AHT 1.0 S                           |
| Cycles  | 2                                   |
| Condensation test result  | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type   | snapped into marker carrier         |

### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2                          |

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

## Drawings

# Snap-in markers - UC-EM (20X7) - 0825499

Pictogram



## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 8.0    | 27149129 |
| eCl@ss 9.0    | 27400629 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

## Accessories

Accessories

Magazine

## Snap-in markers - UC-EM (20X7) - 0825499

### Accessories

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>