

Replacement electronics module - IBS STME 24 BK DIO 8/8/3-T - 2752961

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Replacement module electronics for IBS ST (ZF) 24 BK DIO 8/8/3-T


The photo shows the complete module

Your advantages

- Remote bus connections using copper technology
- Electrical isolation
- 8 digital outputs
- 8 digital inputs
- Diagnostic and status indicators
- DIN rail mounting



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 108625
GTIN	4017918108625
Weight per Piece (excluding packing)	315.800 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Ambient conditions

Degree of protection	IP20
----------------------	------

Replacement electronics module - IBS STME 24 BK DIO 8/8/3-T - 2752961

Technical data

General

Mounting type	DIN rail
Net weight	315.8 g

Connection data

Connection method	Screw connection
Stripping length	8 mm

Standards and Regulations

Connection in acc. with standard	CUL
----------------------------------	-----

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27259200
eCl@ss 5.1	27242600
eCl@ss 6.0	27242600
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604
eCl@ss 9.0	27242604

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC002584
ETIM 5.0	EC001599
ETIM 6.0	EC001599
ETIM 7.0	EC001599

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	39121311
UNSPSC 13.2	32151602

Replacement electronics module - IBS STME 24 BK DIO 8/8/3-T - 2752961

Classifications

UNSPSC

UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
---------------	--	---	---------------

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
----------------	--	---	---------------

EAC		EAC-Zulassung
-----	--	---------------

cULus Recognized	
------------------	--