

Adapter cable - CABLE-15/8/250/RSM/INDEL - 2902338

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable adapter for PSR over-speed safety relays (PSR-RSM4 and PSR-MM30), 15/8-pos., cable length: 2.5 m, for controller: INDEL




The figure shows the version CABLE-15/8/250/RSM/SIMO611D

Your advantages

- ✓ Option to connect to safe PSR-RSM4 and PSR-MM30 over-speed safety relays
- ✓ Suitable for connection to the existing motor feedback interface of an electrical drive
- ✓ Controller type:INDEL
- ✓ 15-pos. D-SUB connection
- ✓ Length of connecting cable to over-speed safety relay: 2.5 m



Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 4 6 3 5 6 6 5 5 6 4 4
GTIN	4046356655644
Weight per Piece (excluding packing)	161.000 g
Custom tariff number	85444290
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Fixed cable length	2.5 m
--------------------	-------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Adapter cable - CABLE-15/8/250/RSM/INDEL - 2902338

Technical data

General

Connection 1	To the device
Connection method	RJ45
Connection 2	Encoder / PLC
Connection method	D-SUB-15 male/D-SUB-15 female
Number of positions	15
Cable resistance	≤ 260 Ω/km
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield
	Soldering on D-SUB housing
Conductor cross section	0.48 mm ² (AWG 26)

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27149290
eCl@ss 4.0	27371100
eCl@ss 4.1	27371100
eCl@ss 5.0	27149200
eCl@ss 5.1	27149200
eCl@ss 6.0	27149200
eCl@ss 7.0	27149290
eCl@ss 8.0	27149290
eCl@ss 9.0	27149290

ETIM

ETIM 2.0	EC001449
ETIM 3.0	EC001449
ETIM 4.0	EC002608
ETIM 5.0	EC002783
ETIM 6.0	EC002783
ETIM 7.0	EC002783

UNSPSC

UNSPSC 6.01	30211901
UNSPSC 7.0901	39121501
UNSPSC 11	39121501
UNSPSC 12.01	39121501
UNSPSC 13.2	26121641

Adapter cable - CABLE-15/8/250/RSM/INDEL - 2902338

Classifications

UNSPSC

UNSPSC 18.0	26121641
UNSPSC 19.0	26121641
UNSPSC 20.0	26121641
UNSPSC 21.0	26121641