

Protective hose - WP-PA HF 42,5 BK - 3241089

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

RoHS

Key Commercial Data

Packing unit	25 M
Minimum order quantity	25 M
GTIN	 4 046356 736534
GTIN	4046356736534
Weight per Piece (excluding packing)	154.000 g
Custom tariff number	39173200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Inner diameter (f)	36 mm
Outside diameter	42.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Short-term temperature	150 °C
Degree of protection	IP67

General

Color	black
Type	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PA

Protective hose - WP-PA HF 42,5 BK - 3241089

Technical data

General

Bending radius, static	90 mm
Bending radius, dynamic	150 mm
Tensile strength	100 N

Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27430304
eCl@ss 8.0	27430304
eCl@ss 9.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177
ETIM 6.0	EC001177
ETIM 7.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734

Protective hose - WP-PA HF 42,5 BK - 3241089

Classifications

UNSPSC

UNSPSC 21.0	40141734
-------------	----------

Approvals

Approvals

Approvals

DNV / LR / UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approval details

DNV		http://exchange.dnv.com/tari/
-----	--	---

LR		http://www.lr.org/en
----	---	---

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
---------------	---	---

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx
------------------------	---	---

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G HF IP66 PG36 BK - 3240894



Cable gland, Pg thread, IP66 protection, straight

Protective hose - WP-PA HF 42,5 BK - 3241089

Accessories

Screw connection - WP-G HF IP66 M40 BK - 3240901



Cable gland, metric thread, IP66 protection, straight

Screw connection - WP-G HF IP69K PG36 BK - 3240880



Cable gland, Pg thread, IP68/69k protection, straight

Screw connection - WP-G HF IP69K M40 BK - 3240887



Cable gland, metric thread, IP68/69k protection, straight

Screw connection - WP-GA HF IP66 PG36 BK - 3240922



Cable gland, Pg thread, IP66 protection, angled

Screw connection - WP-GA HF IP69K PG36 BK - 3240908



Cable gland, Pg thread, IP68/69k protection, angled

Protective hose - WP-PA HF 42,5 BK - 3241089

Accessories

Screw connection - WP-GA HF IP69K M40 BK - 3240915



Cable gland, metric thread, IP68/69k protection, angled

Screw connection - WP-GR HF IP66 PG36 BK - 3240950



Cable gland, Pg thread, IP66 protection, with strain relief

Screw connection - WP-GR HF IP69K PG36 BK - 3240936



Cable gland, Pg thread, IP68/69k protection, with strain relief

Mounting material

Hose holder with cover - WP-BASE C PA HF 42,5 BK - 3240964



Hose holder with cover

Hose clamp - WP-BASE HF 45 - 3240973



Hose clamps

Protective hose - WP-PA HF 42,5 BK - 3241089

Accessories

Protective hose fixing bracket - WP-BASE A M40 - 3241087



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Transition sleeve from hose to cable - WP-EC TPE HF 42,5 BK - 3240980



End sleeves, transition sleeves, from hose to cable

Cable protection end sleeve - WP-SC PA HF 42,5 BK - 3240987



End sleeves as cable protection