

Protective hose - WP-PA HF-SL 21,2 BK - 3240845

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide protective hose, inflammability class V0, UV resistant

RoHS

Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 736619
GTIN	4046356736619
Weight per Piece (excluding packing)	99.990 g
Custom tariff number	39173200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Inner diameter (f)	16.5 mm
Outside diameter	21.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Short-term temperature	120 °C
Degree of protection	IP67

General

Color	black
Type	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	HB
Material	PA

Protective hose - WP-PA HF-SL 21,2 BK - 3240845

Technical data

General

Bending radius, static	40 mm
Bending radius, dynamic	120 mm
Tensile strength	100 N

Standards and Regulations

Resistance to UV radiation	yes
Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27430304
eCl@ss 8.0	27430304
eCl@ss 9.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177
ETIM 6.0	EC001177
ETIM 7.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734

Protective hose - WP-PA HF-SL 21,2 BK - 3240845

Classifications

UNSPSC

UNSPSC 21.0	40141734
-------------	----------

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
---------------	---	---
