

Protective hose - WP-SPIRAL PVC C 10 - 3240849

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose, spring steel wire with PVC coating, highly stranded

RoHS

Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 736657
GTIN	4046356736657
Weight per Piece (excluding packing)	53.000 g
Custom tariff number	39173200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Inner diameter (f)	7 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Short-term temperature	100 °C
Degree of protection	IP68

General

Color	gray
Type	Spring steel wire with soft PVC coating
Components	Free from silicone and cadmium
Material	PVC
Bending radius, static	8 mm

Protective hose - WP-SPIRAL PVC C 10 - 3240849

Technical data

General

Bending radius, dynamic	20 mm
Tensile strength	100 N

Standards and Regulations

Resistance to UV radiation	no
Halogen-free	no

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27430304
eCl@ss 8.0	27430304
eCl@ss 9.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177
ETIM 6.0	EC001177
ETIM 7.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Protective hose - WP-SPIRAL PVC C 10 - 3240849

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G PP HF PG7 - 3240988



Cable gland made from PP with Pg thread, IP65 protection

Screw connection - WP-G PP HF M10 - 3240995



Cable gland made from PP with metric thread, IP65 protection

Screw connection - WP-GT PP HF PG7 - 3241002



Cable gland made from PP with Pg thread, rotatable, IP54 protection

Protective hose - WP-SPIRAL PVC C 10 - 3240849

Accessories

Screw connection - WP-GT PP HF M12 - 3241010



Cable gland made from PP with metric thread, rotatable, IP54 protection

Mounting material

Hose clamp - WP-BASE HF 9-10 - 3240965



Hose clamps

Protective cap

Cable protection end sleeve - WP-SC HF 10 - 3241016



End sleeves as cable protection