

Protective hose - WP-STEEL S 14 - 3240687


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective hose in stainless steel

RoHS

Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 736916
GTIN	4046356736916
Weight per Piece (excluding packing)	99.990 g
Custom tariff number	83071000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Inner diameter (f)	11 mm
Outside diameter	14 mm

Ambient conditions

Ambient temperature (operation)	-200 °C ... 600 °C
Degree of protection	IP40

General

Color	silver
Type	Spirals
Components	halogen-free
Material	Stainless steel 1.4301/AISI 304
Bending radius, static	28 mm
Bending radius, dynamic	70 mm

Protective hose - WP-STEEL S 14 - 3240687

Technical data

General

Tensile strength	500 N
------------------	-------

Standards and Regulations

Halogen-free	yes
--------------	-----

Classifications

eCl@ss

eCl@ss 4.0	27140900
eCl@ss 4.1	27140900
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27430301
eCl@ss 8.0	27430301
eCl@ss 9.0	27430301

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179
ETIM 6.0	EC001179
ETIM 7.0	EC001179

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Accessories

Accessories

Corrugated pipe screw connection

Protective hose - WP-STEEL S 14 - 3240687

Accessories

Screw connection - WP-G BRASS IP40 PG9 - 3241038



Cable gland made from brass with Pg thread, IP40 protection

Screw connection - WP-G BRASS IP40 M12 - 3241045



Cable gland made from brass with metric thread, IP40 protection

Screw connection - WP-GT BRASS PG9 - 3241024



Cable gland made from brass with Pg thread, rotatable, IP40 protection

Screw connection - WP-GT BRASS M12 - 3241031



Cable gland made from brass with metric thread, rotatable, IP40 protection

Mounting material

Hose clamp - WP-BASE HF 14 - 3240967



Hose clamps

Protective cap

Protective hose - WP-STEEL S 14 - 3240687

Accessories

Cable protection end sleeve - WP-SC BRASS 14 - 3241066



End sleeves as cable protection, made of brass