

# Memory - CF FLASH 256MB - 2988780

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Program and configuration memory, plug-in, 256 MB

## Product Description

Program and configuration memory to save the application programs and other files in the file system of the PLC. Alternatively, a program and configuration memory with integrated license is available to disconnect various function blocks.



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 184984
GTIN	4046356184984
Weight per Piece (excluding packing)	14.700 g
Custom tariff number	85235110
Country of origin	Taiwan

## Technical data

### Dimensions

Height	42.8 mm
Depth	3.3 mm
Width	36.4 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### General

Weight	9 g
Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

# Memory - CF FLASH 256MB - 2988780

## Technical data

### Environmental Product Compliance

	No hazardous substances above threshold values
--	--

## Classifications

### eCl@ss

eCl@ss 4.0	27250200
eCl@ss 4.1	27250200
eCl@ss 5.0	27242200
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

### ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005
UNSPSC 18.0	32101606
UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606