

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Hose holder with cover



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710664
GTIN	4046356710664
Weight per Piece (excluding packing)	4.130 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Hole diameter	5.5 mm
Diameter	13 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	black
Components	halogen-free
Flammability rating according to UL 94	V2
Material	PA

Standards and Regulations

Connection in acc. with standard	UL
----------------------------------	----

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	23159090
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439208
eCl@ss 8.0	27439208
eCl@ss 9.0	23159090

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000127
ETIM 5.0	EC001171
ETIM 6.0	EC001171
ETIM 7.0	EC000368

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411
UNSPSC 18.0	31162906
UNSPSC 19.0	31162906
UNSPSC 20.0	31162906
UNSPSC 21.0	31162906

Approvals

Approvals

Hose holder with cover - WP-BASE C PA HF 13,0 BK - 3240959

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 13,0 BK - 3240681



Polyamide protective hose, inflammability class V0, UV resistant

Protective hose - WP-PA HF-HB 13,0 BK - 3240839



Polyamide protective hose, inflammability class HB, UV resistant
