


Profile - UM122-PROFIL 235CM - 2735438

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Profile PC board base, with a constructional width of 122 mm and a fixed length of 235 cm



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 589561
GTIN	4017918589561
Weight per Piece (excluding packing)	1,116.670 g
Custom tariff number	39162000
Country of origin	Germany

Technical data

Product properties

Brief article description	Profile
Type	UM122-PROFIL 235CM
Order No.	2735438
Housing type	Press-drawn section housings
Type	Basic profile

Dimensions

Length	235 cm
Profile width (external)	127.5 mm
Profile width (internal)	122 mm

Material specifications

Housing material	PVC
------------------	-----

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

Profile - UM122-PROFIL 235CM - 2735438

Technical data

Packaging specifications

Pieces per package	1
Denomination packing units	Pcs.

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Profile - UM122-PROFIL 235CM - 2735438

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	--	---------

Accessories

Accessories

Component housing cover

Covering hood - UM122-A/U92 - 2909455



Press-drawn section housings, Cover, 92 mm wide, width: 92 mm, Note: length of the cover = length of the PCB - 1.8 mm

Cover profile

Insert strip - AP-ES - 5022685



Insert strip, white, unlabeled, mounting type: insert, for terminal block width: 35 mm, lettering field size: 35 x 500 mm

Insert strip - AP-ES - 5022685



Insert strip, white, unlabeled, mounting type: insert, for terminal block width: 35 mm, lettering field size: 35 x 500 mm

Profile - UM122-PROFIL 235CM - 2735438

Accessories

Marker carriers

Module marker carrier - PMB - 1004364



Phoenix module marker carrier, for labeling modules and PCBs, for hole diameter 3.9 to 4.1 mm, thickness of wall or board 1.5 - 2.0 mm, labeling with insert strips ESL, EST or ES/LP-BW-GB, lettering field: 29 x 8 mm

Module marker carrier - PMB - 1004364



Phoenix module marker carrier, for labeling modules and PCBs, for hole diameter 3.9 to 4.1 mm, thickness of wall or board 1.5 - 2.0 mm, labeling with insert strips ESL, EST or ES/LP-BW-GB, lettering field: 29 x 8 mm

Marker pen

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Mounting material

Foot element - UM122-FE - 2909471

UM 122 FE foot element, for UM 122 profile housing



Profile - UM122-PROFIL 235CM - 2735438

Accessories

Foot element - UM122-FE - 2909471

UM 122 FE foot element, for UM 122 profile housing



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>