

## Tool set - SF-BIT SET - 1212545

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Bit set, with SF-UBH universal bit holder, with 25 mm long bladed/crosshead bits (PZ and PH), 10-part, in compact plastic box

### Product Description

Set includes 1 each of quick-change bit holder, bits: PH1, PH2, PH3, PZ1, PZ2, PZ3: 0.8 x 5.5 x 25 mm, 1.0 x 5.5 x 25 mm, 1.2 x 6.5 x 25 mm.

### Your advantages

- ✓ Bits can be accessed quickly thanks to the user-friendly, one-handed opening mechanism
- ✓ Clearly arranged storage
- ✓ Equipped with hardened bits for durability
- ✓ Bit set, in compact plastic box, with quick-change bit holder and the following 25 mm long bits: 0.8 x 5.5, 1.0 x 5.5, 1.2 x 6.5, PH1, PH2, PH3, PZ1, PZ2, PZ3

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589802
GTIN	4046356589802
Weight per Piece (excluding packing)	97.000 g
Custom tariff number	82079030
Country of origin	Czech Republic
Note	Made to Order (non-returnable)

### Technical data

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Classifications

#### eCl@ss

eCl@ss 10.0.1	21040411
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400

## Tool set - SF-BIT SET - 1212545

### Classifications

#### eCl@ss

eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21049219
eCl@ss 8.0	21049219
eCl@ss 9.0	21040411

#### ETIM

ETIM 4.0	EC000149
ETIM 5.0	EC002120
ETIM 6.0	EC002119
ETIM 7.0	EC002119

#### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701
UNSPSC 18.0	27112814
UNSPSC 19.0	27112814
UNSPSC 20.0	27112814
UNSPSC 21.0	27112814

### Approvals

#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01750
-----	---	--------------------------

