

Stripping machine - WF 1000 - 1212149

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Stripping machine with integrated graphic display, for conductors and cables up to 6 mm in diameter, 230 V version

Your advantages

- ✓ The clamping force automatically adjusts itself to the required extraction force
- ✓ Compact stripping machine for automatically stripping conductors with a cross section of 0.08 to 6 mm²
- ✓ Even special types of insulation, such as PTFE and silicone, can be stripped in addition to standard types
- ✓ Pressure points on sensitive insulation are avoided
- ✓ The stripping dimensions are set individually via knobs and are shown on the large display
- ✓ Multi-strand cables with a diameter of up to 6 mm can also be stripped
- ✓ Partial stripping is supported

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 457026
GTIN	4046356457026
Weight per Piece (excluding packing)	11,250.000 g
Custom tariff number	84798100
Country of origin	Germany

Technical data

Dimensions

Length (b)	363 mm
Width (a)	141 mm
Height (c)	221 mm
Diameter, conductor entry opening	6 mm

General

Power consumption	160 VA
-------------------	--------

Stripping machine - WF 1000 - 1212149

Technical data

General

Maximum throughput	6
Min. cross section	0.08 mm ²
Max. cross section	6 mm ²
Minimum stripping length	2 mm
Maximum stripping length	20 mm
Partial stripping length range minimum	2 mm
Partial stripping length range maximum	20 mm
Weight	9.5 kg
Min. cross section	0.08 mm ²
Max. cross section	6 mm ²
AWG min	32
AWG max	14

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	17130102
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	17130100
eCl@ss 6.0	17130100
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101
eCl@ss 9.0	17130102

ETIM

ETIM 2.0	EC000142
ETIM 3.0	EC000142
ETIM 4.0	EC000163
ETIM 5.0	EC002778
ETIM 6.0	EC002778
ETIM 7.0	EC002778

UNSPSC

UNSPSC 6.01	23171604
-------------	----------

Stripping machine - WF 1000 - 1212149

Classifications

UNSPSC

UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01549
-----	---	--------------------------

Accessories

Accessories

Knife

Spare knife - WF 1000/SB - 1212279



Spare knife for stripping machine

Magazine

Accessories - WF 1000/COV - 1212417



Waste holder for stripping machine

Stripping machine - WF 1000 - 1212149

Accessories

Mounting material

Replacement retaining jaw - WF 1000/CJ - 1212415



Replacement jaws for stripping machine

Operating stylus

Accessories - WF 1000/TR - 1212416



Start key trigger for stripping machine