

Mounting material - HC-ALU 6 DECO 150 GY - 2200915

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Decorative strip for HC-ALU panel mounting base

Your advantages

- ✓ Item is from the HC-ALU product range
- ✓ Aluminum press-drawn section
- ✓ Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- ✓ Available in overall widths 53.5 mm ... 161 mm
- ✓ Degree of protection up to IP65
- ✓ Usable as handheld and wall housing
- ✓ Optional EMC seals available

RoHS

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 716840
GTIN	4046356716840
Weight per Piece (excluding packing)	5.940 g
Custom tariff number	39269097
Country of origin	Hungary
Note	Made to Order (non-returnable)

Technical data

General

Housing type	Panel mounting base
Color (RAL)	gray

Dimensions

Mounting material - HC-ALU 6 DECO 150 GY - 2200915

Technical data

Dimensions

Length	148.4 mm
--------	----------

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC002498
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501