


Side element - UM108-SEFE/L-A73 BK - 2707628

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Lateral element with foot, 5 mm wide (left), for assembly on NS 32 or NS 35/7.5, tall design, for 73 mm-wide U-profile cover

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 903152 |
| GTIN | 4017918903152 |
| Weight per Piece (excluding packing) | 18.100 g |
| Custom tariff number | 85389099 |
| Country of origin | Poland |
| Note | Made to Order (non-returnable) |

Technical data

Product properties

| | |
|---------------------------|------------------------------|
| Brief article description | Side element |
| Type | UM108-SEFE/L-A73 BK |
| Order No. | 2707628 |
| Housing type | Press-drawn section housings |
| Type | Lateral element (left) |

Dimensions

| | |
|---------------------------------|----------------|
| Profile PCB width (selectable): | 108 mm [UM108] |
| Depth [d] | 125 mm |

Material specifications

| | |
|--|-------|
| Color (RAL) | black |
| Flammability rating according to UL 94 | V0 |

Packaging specifications

| | |
|----------------------------|------|
| Pieces per package | 10 |
| Denomination packing units | Pcs. |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|------------|---|

Side element - UM108-SEFE/L-A73 BK - 2707628

Technical data

Environmental Product Compliance

| | |
|--|--|
| | No hazardous substances above threshold values |
|--|--|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27182701 |
| eCl@ss 4.0 | 27180400 |
| eCl@ss 4.1 | 27180400 |
| eCl@ss 5.0 | 27180500 |
| eCl@ss 5.1 | 27180500 |
| eCl@ss 6.0 | 27180800 |
| eCl@ss 7.0 | 27182701 |
| eCl@ss 8.0 | 27182701 |
| eCl@ss 9.0 | 27182701 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC002779 |
| ETIM 6.0 | EC002779 |
| ETIM 7.0 | EC002779 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11 | 31261501 |
| UNSPSC 12.01 | 31261501 |
| UNSPSC 13.2 | 31261501 |
| UNSPSC 18.0 | 31261501 |
| UNSPSC 19.0 | 31261501 |
| UNSPSC 20.0 | 31261501 |
| UNSPSC 21.0 | 31261501 |

Approvals

Approvals

Approvals

UL Recognized

Side element - UM108-SEFE/L-A73 BK - 2707628

Approvals

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868