

Carrier for conductor marking collar - SD-WMTB (70X10) - 0826530

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Carrier for conductor marking collar, black, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 16 mm, lettering field size: 70 x 10 mm

Your advantages

- The printed individual markers are pushed onto the corresponding holders
- Cable markers for marking cables and conductors with larger cross sections

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 414500
GTIN	4046356414500
Weight per Piece (excluding packing)	0.750 g
Custom tariff number	39269097
Country of origin	Sweden

Technical data

Dimensions

Length (b)	70 mm
Width (a)	10 mm

General

Color	black
Type	Marking strip/label
Material	Polyvinyl chloride
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed

Carrier for conductor marking collar - SD-WMTB (70X10) - 0826530

Technical data

General

Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27149100
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504

Carrier for conductor marking collar - SD-WMTB (70X10) - 0826530

Classifications

UNSPSC

UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Cable tie

Cable tie - WT-HF 2,5X98 - 3240732



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X140 - 3240744



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X200 - 3240760



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,6X200 - 3240740



Cable binders for quick and secure bundling, standard version

Carrier for conductor marking collar - SD-WMTB (70X10) - 0826530

Accessories

Cable tie - WT-HF 4,5X290 - 3240764



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X360 - 3240768



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 2,5X98 BK - 3240733



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 3,6X140 BK - 3240745



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X200 BK - 3240761



Cable binders for quick and secure bundling, standard version

Carrier for conductor marking collar - SD-WMTB (70X10) - 0826530

Accessories

Cable tie - WT-HF 2,6X200 BK - 3240741



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X290 BK - 3240765



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HF 4,5X360 BK - 3240769



Cable binders for quick and secure bundling, standard version
