

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348580506](#)
Status: **Active**
Overview: [HSAutoLink Interconnect Systems](#)
Description: HSAutoLink II Vertical Sealed Header, 12 Circuits

Documents:

3D Model	Packaging Specification PK-31301-766 (PDF)
Drawing (PDF)	Packaging Specification PK-34858-001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-34858-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	PCB Headers
Series	34858
Application	Automotive, Signal, Wire-to-Board
Comments	Higher current capability depending of the connector loading, please contact Molex for further technical details.. 36 V max (Power lines) / 60 V max (Differential pair – Wire/shield or Wire/Wire)., Higher current capability depending of the connector loading, please contact Molex for further technical details.. 36 V max (Power lines) / 60 V max (Differential pair – Wire/shield or Wire/Wire).
Overview	HSAutoLink Interconnect Systems
Product Name	HSAutoLink II
UPC	884982730816

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.538/g
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.406µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34858 Series](#)

Electrical

Current - Maximum per Contact 1.5A
Voltage - Maximum 36V

Material Info**Reference - Drawing Numbers**

Packaging Specification PK-31301-766, PK-34858-001-001
Product Specification PS-34858-001-001
Sales Drawing SD-34858-001-000

This document was generated on 02/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION