

Shrink sleeve - WMS 2,4 (EX4)R YE - 0800300

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, yellow, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK W: without print, unperforated, mounting type: slide-on, cable diameter range: 0.8 ... 2.4 mm, lettering field size: 4 x 30000 mm

Your advantages

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- UL 224 (125°C, 600 V, all tubing)
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- Individual markers can be cut to any length up to 1 m



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 625975
GTIN	4046356625975
Weight per Piece (excluding packing)	195.000 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	30 m
Width (a)	4 mm
Cable diameter	0.8 mm ... 2.4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Shrink sleeve - WMS 2,4 (EX4)R YE - 0800300

Technical data

General

Color	yellow
Base element material	polyolefine
Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Classifications

eCl@ss

eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530

Shrink sleeve - WMS 2,4 (EX4)R YE - 0800300

Classifications

ETIM

ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	--	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	--	---	---------------

Accessories

Accessories

Ink ribbon

Shrink sleeve - WMS 2,4 (EX4)R YE - 0800300

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm
