

PRODUCT-DETAILS

# T4 P FP 3p EF

# T4 P FP 3p EF



## General Information

Extended Product Type	T4 P FP 3p EF
Product ID	1SDA054737R1
EAN	8015644558512
Catalog Description	T4 P FP 3p EF
Long Description	FIXED PART PLUG-IN FOR C.BREAKER TMAX THREE-POLE WITH EXTENDED FRONT TERMINALS T4

## Ordering

E-Number (Sweden)	3180872
EAN	8015644558512
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

## Dimensions

Product Net Width	105 mm
Product Net Height	209 mm
Product Net Depth / Length	50 mm
Product Net Weight	1 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	72 mm
Package Level 1 Height	72 mm
Package Level 1 Depth / Length	306 mm
Package Level 1 Gross Weight	1.2 kg
Package Level 1 EAN	8015644558512

## Additional Information

Device	Fixed Part
Number of Poles	3
Product Main Type	SACE Tmax T
Product Name	Accessory
Product Type	FP
Rated Operational Voltage	690 V AC 750 V DC
Standards	IEC 60947
Sub-type	T4
Suitable For	T4
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Plug-In Circuit-Breakers Front Extended
Test Voltage at Industrial Frequency for 1 Minute	not applicable V
Version	P

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210004D0203
Declaration of Conformity - CE	1SDL000165R0001
Environmental Information	1SDL000143R0
Instructions and Manuals	1SDH000436R0811
Instructions and Manuals (Part 2)	ITSCE-RH0100001
RoHS Information	1SDL000200R0001

## Classifications

ETIM 7	EC002043 - Chassis part power circuit breaker
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

