

PRODUCT-DETAILS

T5 400 P FP 3p EF

T5 400 P FP 3p EF



General Information

Extended Product Type	T5 400 P FP 3p EF
Product ID	1SDA054749R1
EAN	8015644558703
Catalog Description	T5 400 P FP 3p EF
Long Description	FIXED PART PLUG-IN FOR C.BREAKER TMAX THREE-POLE WITH EXTENDED FRONT TERMINALS T5 400

Ordering

E-Number (Sweden)	3180874
EAN	8015644558703
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Dimensions

Product Net Width	171 mm
Product Net Height	209 mm
Product Net Depth / Length	50 mm
Product Net Weight	1.5 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	131 mm
Package Level 1 Height	131 mm
Package Level 1 Depth / Length	313 mm
Package Level 1 Gross Weight	1.708 kg
Package Level 1 EAN	8015644558703

Additional Information

Device	Fixed Part
Number of Poles	3
Product Main Type	SACE Tmax T
Product Name	Accessory
Product Type	FP
Rated Operational Voltage	690 V AC 750 V DC
Rated Uninterrupted Current (I _u)	400 A
Standards	IEC 60947
Sub-type	T5
Suitable For	T5
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Plug-In Circuit-Breakers Front Extended
Test Voltage at Industrial Frequency for 1 Minute	not applicable V
Version	P

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210004D0203
Declaration of Conformity - CE	1SDL000165R0001
Environmental Information	1SDL000143R0
Instructions and Manuals	1SDH000437R0001
Instructions and Manuals (Part 2)	ITSCE-RH0100001
RoHS Information	1SDL000200R0001

Classifications

ETIM 6	EC002043 - Chassis part power circuit breaker
ETIM 7	EC002043 - Chassis part power circuit breaker
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

