

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0369220802](#)  
**Status:** **Active**  
**Overview:** [Ditto Wire-to-Wire Interconnects](#)  
**Description:** Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 150.00mm Length, 8 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |  |
|------------------------|--|
| Product Family         | Cable Assemblies                                 |
| Series                 | <a href="#">36922</a>                            |
| Application            | Power, Wire-to-Wire                              |
| Assembly Configuration | Dual Ended Connectors                            |
| Connector to Connector | Ditto-to-Ditto                                   |
| Overview               | <a href="#">Ditto Wire-to-Wire Interconnects</a> |
| Product Name           | Ditto  |
| Type                   | Discrete Wire Assembly                           |
| UPC                    | 193264209064                                     |

**Physical**

|                                |                               |
|--------------------------------|-------------------------------|
| Cable Length                   | 150.00mm                      |
| Circuits (Loaded)              | 8                             |
| Color - Resin                  | Black                         |
| Gender                         | Hermaphroditic-Hermaphroditic |
| Lock to Mating Part            | Yes                           |
| Material - Metal               | Tin Brass                     |
| Material - Plating Mating      | Tin                           |
| Material - Plating Termination | Tin                           |
| Material - Resin               | Nylon                         |
| Net Weight                     | 16.195/g                      |
| Number of Rows                 | 1                             |
| Packaging Type                 | Bag                           |
| Pitch - Mating Interface       | 3.00mm                        |
| Single Ended                   | No                            |
| Termination Interface: Style   | Crimp or Compression          |
| Wire Insulation Diameter       | 1.35-1.70mm                   |
| Wire Size AWG                  | 20                            |
| Wire/Cable Type                | UL 1061                       |

**Electrical**

|                               |            |
|-------------------------------|------------|
| Current - Maximum per Contact | 4.2A       |
| Voltage - Maximum             | 350V AC/DC |

**Material Info**

**Reference - Drawing Numbers**

|               |               |
|---------------|---------------|
| Sales Drawing | 369220800-000 |
|---------------|---------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[36922 Series](#)

**Mates With**

Ditto Hermaphroditic Crimp Housing [150170](#)

**Use With**

Ditto Hermaphroditic Terminals [150200](#)

<br>Ditto TPA Retainer [150212](#)