

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0369240410](#)
Status: **Active**
Overview: [Mini-Fit Sr. Power Connectors](#)
Description: Mini-Fit Sr.-to-Mini-Fit Sr. Off-the-Shelf (OTS) Cable Assembly, 10.00mm Pitch, Single Row, 1.0m Length, 4 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	36924
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Comments	Terminal Position Assurance (TPA) Clip Included, Terminal Position Assurance (TPA) Clip Included
Connector to Connector	Mini-Fit Sr.-to-Mini-Fit Sr.
Overmolded	No
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
Type	Discrete Wire Assembly
UPC	193264249800

Physical

Cable Length	1.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	476.950/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	10.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.60mm max.
Wire Size AWG	8
Wire/Cable Type	UL 1015

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Sales Drawing	369240400-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[36924](#) Series

Mates With

4 Circuit Plug Housing [428180412](#) , [42819](#)

 4 Circuit Right-Angle Headers, [42820](#)

Use With

Terminal Position Assurance (TPA) Clip
Included. [42815](#) Female Crimp Terminal