

USB 3.0 SuperSpeed Adapter - USB-A to USB-A, M/F, Down Angle, Black

MODEL NUMBER: U324-000-DN







Converts a standard USB port into a more convenient down-angled USB port in tight spaces, such as behind furniture or against a wall.

Features

One-Piece Adapter Connects Computers, Printers, Modems and Other USB Equipment
This palm-sized USB adapter connects your computer, laptop or other compatible USB-A device, such as
a Chromebook or Surface Pro tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or
other peripheral. It supports USB 3.0 data transfer speeds up to 5 Gbps, which is 10 times faster than
USB 2.0. The fully molded piece is small enough to carry in your pocket, purse or laptop bag.

Down-Angle USB-A Port Makes Connecting and Disconnecting Easier in Tight Spaces
The female USB connector is designed at a 90-degree down angle, which makes it easier to connect
cables where space is at a premium. This helps you, for instance, save space in your workspace by letting
you push your PC flush against the wall or the back of a cabinet. Instead of leaving space in the rear for
protruding USB cables, the U324-000-DN allows you to connect cables parallel to your computer.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 90-degree-angled form factor is ideal for tight spaces, such as flush against a wall
- Supports USB 3.0 SuperSpeed data transfer rates up to 5
 Gbps—10x faster than USB 2.0
- Durable one-piece molded adapter fits easily in pocket or bag for connecting anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Create a USB connection in a hard-to-reach space, such as against a wall or behind a desk

Package Includes

U324-000-DN USB 3.0
 SuperSpeed Adapter

Specifications

OVERVIEW		
UPC Code	037332248688	
PHYSICAL		
Color	Black	
Material of Construction	PVC	





Unit Packaging Type	Polybag	
Offit Fackaging Type	Folybag	
ENVIRONMENTAL		
Operating Temperature Range	32 to 122 F (0 to 50 C)	
Storage Temperature Range	-4 to 140 F (-20 to 60 C)	
Relative Humidity	10 - 90%, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	USB 3.0 A (FEMALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Technology	USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)	
CERTIFICATIONS		
Certifications	Tested to RoHS and REACH	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies