

USB 3.0 SuperSpeed Extension Cable - USB-A to USB-A, M/F, Blue, 16 ft.

MODEL NUMBER: U324-016



Extension cord connects two devices with USB-A connectors or extends your existing USB cable by 16 feet.

Features

16-Foot Extension Cable Connects Computers, Printers, Modems and Other USB Equipment

This USB 3.0 SuperSpeed Type-A Extension Cable (M/F) attaches to your current USB 3.0 cable to extend it by 16 feet. It connects your computer, laptop or other compatible USB 3.0 device, such as a Chromebook or Surface Pro tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. The 16-foot length allows you great flexibility in placing equipment with respect to the power outlet.

Transfers Data at SuperSpeed Transfer Rates up to 5 Gbps

The U324-016 supports USB 3.0 speeds up to 5 Gbps—10 times the speed of USB 2.0—and better power efficiency with no device polling and lower active and idle power requirements. The cable's bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times. Sync-N-Go technology allows the cable to quickly detect and sync the connected devices. The cable is backward compatible with previous USB generations, allowing you to use it with legacy devices.

Highlights

- Recommended for connecting computers, hard drives and other USB-A devices
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Bi-directional data interface allows data to flow both directions simultaneously
- 16 ft. length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 16 ft. extension cord

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 16 ft. to more easily place a device
- Provide a high-quality replacement for a worn-out or missing power cord

System Requirements

- Devices and cable with USB-A connectors (USB 3.0 capability required to reach USB 3.0 speeds)

Package Includes

- U324-016 USB 3.0 SuperSpeed Extension Cable, A to A, M/F, Blue, 16 ft.



Specifications

OVERVIEW	
UPC Code	037332241467
INPUT	
Cable Length (ft.)	16
Cable Length (m)	4.87
Cable Length (in.)	192
Cable Length (cm)	487.68
Product Length (in.)	192
Product Length (cm.)	487.68
Product Length (ft.)	16
Product Length (m.)	4.87
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5MM
Color	Blue
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.43
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	-43 to 158 F (-40 to 70 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold



FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>