

USB 3.1 Gen 2 (10 Gbps) USB-C to M.2 NGFF SATA SSD (B-Key) Enclosure Adapter with UASP Support, Thunderbolt™ 3 Compatible

MODEL NUMBER: U457-1M2-SATAG2



Durable lightweight enclosure connects an M.2 NGFF drive to your computer's USB-C or Thunderbolt™ 3 port and performs fast file transfers at USB 3.1 Gen 2 speeds. UASP-enabled for 70% more speed with UASP host controller.

Description

The U457-1M2-SATAG2 USB 3.1 Gen 2 USB-C to M.2 NGFF SATA SSD (B-Key) Enclosure Adapter lets you connect a high-performance M.2 NGFF SATA SSD (B-Key) drive to a computer or laptop with a USB-C or Thunderbolt™ 3 port. Not only does it support USB 3.1 Gen 2 data transfer rates up to 10 Gbps, but it reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller.

To share data, just remove the adapter's cover using the included screwdriver, connect the drive to the M.2 NGFF connector, secure it with the included screws, put the cover back, and connect the adapter to your computer's USB-C or Thunderbolt™ 3 port using the included cable. The U457-1M2-SATAG2 supports 2230, 2242, 2260 and 2280 M.2 SATA SSD drive types.

The adapter is plug-and-play, so no software, drivers or external power supply is required, and backward compatible with previous USB generations. A blue LED indicates data is being read, written or transferred. Slim aluminum case tucks conveniently into backpack or laptop bag for use anywhere.

Highlights

- Compatible with 2230, 2242, 2260 and 2280 M.2 drive types
- Supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps
- Works up to 70% faster when connected to UASP host controller
- Durable slim design perfectly sized for backpack or laptop bag
- Plug-and-play—no software, drivers or external power supply

System Requirements

- Computer with USB-C or Thunderbolt™ 3 port (USB 3.1 Gen 2 10 Gbps port required for maximum speed)
- M.2 NGFF SATA drive with B-Key or B+M Key connector (not compatible with M.2 NGFF PCIe SSDs)

Package Includes

- U457-1M2-SATAG2 USB 3.1 Gen 2 USB-C to M.2 NGFF SATA SSD (B-Key) Enclosure Adapter
- USB 3.1 Gen 2 Type-C cable (M/M)
- Mini screwdriver
- Mounting hardware
- Owner's manual

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features



Use an M.2 NGFF SSD as a Pocket-Sized USB Device

- Access an M.2 NGFF SATA SSD (B-Key) drive with a computer or laptop's USB-C or Thunderbolt™ 3 port
- Compatible with 2230, 2242, 2260 and 2280 M.2 drive types
- Supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller
- Blue LED indicates data is being read, written or transferred

Built for Portable Use

- Plug and play—no software, drivers or external power supply needed
- Durable slim aluminum case perfectly sized for backpack or laptop bag
- Enclosed housing protects drive in applications requiring more durability
- USB 3.1 Gen 2 Type-C cable included

Specifications

OVERVIEW	
UPC Code	037332201256
Drives Supported	M.2 NGFF SATA (B-KEY)
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Data)
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Shipping Dimensions (hwd / cm)	3.51 x 14.50 x 13.00
Shipping Dimensions (hwd / in.)	1.38 x 5.71 x 5.12
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.12
Unit Dimensions (hwd / cm)	0,96 x 11 x 4,1
Unit Dimensions (hwd / in.)	0.38 x 4.3 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05



Unit Weight (lbs.)	0.12
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
Power Consumption (Watts)	5
CONNECTIONS	
Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	M.2 NGFF SATA (B-Key)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Driver Required	No
UASP Support	Yes
Technology	SATA/eSATA
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>