

USB-C to USB Type-B Cable (M/M) - USB 3.1, Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: **U422-003-G2**



Connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a device or peripheral with a USB 3.0 Type-B port, such as a hub or external hard drive.

Description

The U422-003-G2 USB 3.1 Gen 2 Cable connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a hub, external hard drive or other peripheral with a USB 3.0 Type-B port. This three-foot cable supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps. A reversible USB-C male connector plugs into a USB port in either direction for fast, fumble-free connection every time.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. Backward compatible with previous USB generations.

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features

Supports USB 3.1 Gen 2 Recommended for smartphones, tablets, laptops, computers, external hard drives, hubs and other compatible devices
 Data transfer speeds up to 10 Gbps—20 times faster than USB 2.0
 Same USB-B male connector as USB 3.0 devices
 Backward compatible with previous USB generations
USB-C Male Connector Fumble-free reversible plug ensures fast, easy connection every time
Premium Construction for Superior Signal Transfer Foil and braid shielding for error-free signal quality and EMI/RFI protection
 Molded nickel-plated connectors and gold-plated contacts
 Integral strain relief for long life
 Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332197375

Highlights

- USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C male connector for fast connection the first time
- Error-free signal quality and EMI/RFI protection
- Backward compatible with previous USB generations

System Requirements

- Device with a USB-C port
- Device with a USB 3.0 Type-B port

Package Includes

- U422-003-G2 USB 3.1 Gen 2 (10 Gbps) Cable, USB-C to USB 3.0 Type-B (M/M), 3 ft.



INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 15.24 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 6.00 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10 to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Technology	USB; USB 3.1 (Gen 2)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>