

## USB-C to USB-A Cable (M/M), USB 3.1 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft.

MODEL NUMBER: **U428-003-G2**



Connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a device or peripheral with a USB-A port.

### Description

The U428-003-G2 USB 3.1 Gen 2 Cable connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a computer, charger or other peripheral with a USB-A port. This three-foot cable supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps. A reversible USB-C male connector plugs into a USB port in either direction for fast, fumble-free connection every time.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. Backward compatible with previous USB generations.

*USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum*

### Features

#### Supports USB 3.1 Gen 2

- Recommended for smartphones, tablets, laptops, computers, hard drives, chargers and other compatible devices
- Data transfer speeds up to 10 Gbps
- Backward compatible with previous USB generations

#### USB-C Male Connector

### Highlights

- USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C male connector for fast connection the first time
- Error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Backward compatible with previous USB generations

### System Requirements

- Device with a USB-C port
- Device with a USB-A port

### Package Includes

- U428-003-G2 USB 3.1 Gen 2 (10 Gbps) Cable, USB-C to USB-A (M/M), 3 ft.



- Fumble-free reversible plug ensures fast, easy connection every time

#### Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Integral strain relief for long life
- Rugged PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332197498
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.12
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10 to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Technology	USB
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>