

USB-C Dock, 4K HDMI, VGA, Gbe, 2x USB-A Ports, 1X USB-C Port, SD Card Reader, 100W PD 3.0

MODEL NUMBER: U442-DOCK3-B



USB-C docking station adds HDMI, Gigabit ethernet, memory card, PD Charging and other ports to turn your Chromebook, MacBook, smartphone, tablet or PC into a complete workstation.

Features

USB-C Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport WorkstationThe U442-DOCK3-B expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting 4K video and audio to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging 3.0-compliant mobile device, connecting to a Gigabit Ethernet network and a lot more—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video SignalsWith a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 4K HDMI Video and Digital AudioTo send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the corresponding port to the display using an HDMI cable (sold separately). The HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz. The VGA port supports high-definition resolutions up to 1920 x 1200, including 1080p, at 60 Hz. A DVI display may be connected to the HDMI port using an HDMI to DVI adapter (sold separately).

Connects Up to 3 USB PeripheralsThe two USB-A hub ports and single USB-C data port accept USB peripherals, such as flash drives, mice, keyboards and printers, and share a maximum 10W (5V 2A) of power. They support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices. The BC 1.2-compliant USB-A port next to the memory card slots provides up to 1.5A of fast-charging power to mobile devices.

Charges the Connected DeviceThe USB-C Power Delivery (PD) port provides power and charging to the PD Charging 3.0-compliant device (such as a MacBook, Chromebook or Android smartphone) the U442-DOCK3-B is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 100W (20V 5A). When the wall charger is unplugged, the unit's PD 3.0 Fast Role Swap feature ensures all data and power connections remain stable.

Accesses a Wired Gigabit Ethernet NetworkThe RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Allows External Memory AccessThe memory card slots support Micro SD and SD/MMC cards for transferring data to and from your connected computer, laptop or tablet. Only one memory card slot can be used at a time.

Built-In USB-C Cable Connects in Either DirectionConnect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. The built-in cable tucks away beneath the compact unit for safe carrying

Highlights

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- HDMI port delivers UHD picture quality at resolutions up to 4K x 2K @ 30 Hz
- Connects you to a wired Ethernet network when Wi-Fi is weak or unavailable
- Powers and charges PD Charging 3.0-compliant devices, such as MacBooks and Chromebooks
- Easy installation with plug-and-play operation—no software required

Applications

- Play video from your laptop or PC on an HDMI or VGA display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Transfer data to and from a USB flash drive or Micro SD or SD/MMC memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging 3.0 port
- Connect a USB microphone/headset to record a podcast or listen to music
- Write a report using a USB



in a pocket, briefcase or laptop bag.

Ready to Use Right Out of the Package Enjoy the convenience of one multiport USB-C docking station instead of several different port converters. The plug-and-play USB-C dock for MacBooks, Chromebooks and other devices requires no software, drivers or external power.

3-Year Warranty and Environmentally Responsible Design The U442-DOCK3-B comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

keyboard with your tablet or
Android smartphone

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
 - Display device with VGA, DVI* or HDMI input
- *Requires adapter (sold separately)

Package Includes

- U442-DOCK3-B USB-C Laptop Docking Station - HDMI, VGA, GbE, 4K, Thunderbolt 3, USB-A, USB-C, PD Charging 3.0, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213495
OUTPUT	
Charging Ports / Amps	3A / 2A / 1.5A
Charging Watts	100
INPUT	
Bus Powered	Yes
Product Length (in.)	9.4
Product Length (cm.)	23.88
Product Length (ft.)	0.78
Product Length (m.)	0.24
BATTERY	
Battery Charging (1.2 Port)	Yes



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power) and Orange (Activity)
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	ABS/Plastic
Unit Dimensions (hwd / in.)	0.55 x 4.8 x 2.8
Unit Packaging Type	Box
Unit Weight (kg)	0.09
Unit Weight (lbs.)	0.20
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	17.1 BTU/Hr
Power Consumption (Watts)	5
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x
CONNECTIONS	
Ports	9
Dock Connectors	USC-C 3.0 Data, (x2) USB-A, Micro SD Memory Card, SD/MMC Memory Card, HDMI, VGA, RJ45, USB-C PD Charging
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE); HDMI (FEMALE); RJ45 (FEMALE); USB C (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE); SD (FEMALE); (2) USB 3.0 A (FEMALE); USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	HDMI: 3840 X 2160 (4K X 2K) @ 30HZ; VGA: 1920 X 1200 (1080P) @ 60HZ
HDMI Specification	1.4
HDCP Specification	1.4



USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
USB Power Delivery (PD) Charging Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; HDMI; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); VGA/SVGA; PD Charging
SD Card Specification	SD; Micro SD
USB Power Delivery (PD) Charging Specification	3.0
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>