

Industrial Cat6 UTP Ethernet Cable (RJ45 M/M), 100W PoE, CMR-LP, IP68, Blue, 33 ft.

MODEL NUMBER: N200P-033BL-IND



Connects Gigabit Ethernet and PoE equipment in industrial environments that require protection against dust and moisture.

Features

Cat6 Cable Recommended for Outdoor or Harsh Indoor Environments

This 33-foot (10-meter) Cat6 CMR-LP outdoor cable is ideal for connecting Gigabit Ethernet networks or digital signage in outdoor applications and other areas where protection from harsh elements is essential, such as factories, warehouses, recycling plants, machine shops and other dusty environments. The RJ45 connectors feature durable enclosures designed to withstand dust, debris and moisture that could threaten your IT infrastructure. Included dust caps protect the connectors when not in use.

IP68 Rating Denotes Resistance to Dust and Water

The IP68 rating means the Cat6 cable is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance. For applications that require IP68 protection, use the industrial cable with a Tripp Lite N206-SB01-IND surface-mount box and a N206-BC01-IND bulkhead coupler or N206-KJ01-IND keystone jack. If only IP44 protection against splashing water from all directions is required, pair the cable with a N206-FP01-IND, N206-FP02-IND or N206-FP04-IND metal wall plate and a N206-BC01-IND bulkhead coupler or N206-KJ01-IND keystone jack.

Supports Power over Ethernet to Save You Money and Give You More Installation Choices

Because this Cat6 cable supports High-Power 100W PoE (71W at device end), it can supply the power to operate compatible data, voice, security and audio/video PoE devices, such as security cameras, VoIP telephones and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

CMR-LP Certified for Cable Installations with Increased Power Levels

UL's Limited Power (LP) certification indicates the N200P-033BL-IND has been evaluated to handle the marked current under installation scenarios without exceeding the temperature rating of the cable. This CMR-LP-certified cable provides a simple way to prepare installations for increased power levels without having to worry about susceptible issues caused by excessive heat.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime

This Cat6 UTP patch cable features a blue PVC jacket. The color-coding allows easy, fast identification in a crowded rack, patch panel or workstation and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Protects Ethernet and digital signage applications in outdoor or harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports 100W PoE (71W at device end) to save you expense of powering devices individually
- UL CMR-LP certified to meet high-temperature safety standards in PoE applications
- Color-coded blue for fast, easy identification in a crowded rack or patch panel

Applications

- Connect Gigabit Ethernet networks or digital signage in factories, warehouses, recycling plants, machine shops and other dusty environments
- Provide Cat6 connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Deliver power to PoE devices mounted in areas that are difficult to reach or have no electrical outlets
- Save money by installing industrial cables that support both power and data, rather than separate power and data cables



Package Includes

- N200P-033BL-IND Industrial
Cat6 UTP Patch Cable - RJ45
M/M, 33 ft. (10 m)

Specifications

OVERVIEW	
UPC Code	037332251985
INPUT	
Cable Length (ft.)	33
Cable Length (m)	10.06
Cable Length (in.)	396
Cable Length (cm)	1005.84
PHYSICAL	
Cable Jacket Rating	CMR-LP
Cable Jacket Type	CMR
Cable Outer Diameter (OD)	6.5 +/- 0.3mm
Cable Shielding	UTP
Color	Blue
Crossover Wiring	Yes
Material of Construction	CMR-LP, PVC, ABS
Snagless Connector	No
Wire Type	Solid
ENVIRONMENTAL	
Operating Temperature Range	14 to 140°F (-10 to 60°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Relative Humidity	0% to 90% RH
Power Provided to Connected Device(s)	100W (71W at device end)
COMMUNICATIONS	
Network Speed	1Gbps



CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
PoE Capability	100W (802.3bt); 15.4W (802.3af); 30W (802.3at); 60W (802.3bt)
PoE Power Budget (Watts)	100
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
Power Over Cable (PoC) Support	No
Technology	Cat6; PoE
SPECIAL FEATURES	
IP68 Rated	Yes
CERTIFICATIONS	
Certifications	Tested to RoHS, REACH, IP68
Protection Rating	IP68
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>