

USB-C Multiport Adapter, 2x USB-A Ports, Card Reader and PD Charging, USB 3.0, White

MODEL NUMBER: U460-002-2AM-C



Adds USB-A, USB-C PD charging and memory card ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U460-002-2AM-C USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and accessing data on a memory card—all at the same time.

The plug-and-play U460-002-2AM-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

The dual USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer. The dedicated BC 1.2-compliant port provides up to 1.5A for charging smartphones and other mobile devices. Both ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) connected to the U460-002-2AM-C. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

The memory card slots support MicroSD, SD, SDHC, SDXC and MMC cards for convenient access to digital photos, camcorder videos, smartphone data and other essential files.

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for adding USB peripherals, powering and charging a PD Charging-compliant mobile device, and accessing memory card data simultaneously Plug-and-play operation with no software, drivers or external power required About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Connect USB Peripherals Dual USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals BC 1.2-compliant port provides up to 1.5A for charging mobile devices Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Backward compatible with USB 2.0 and USB 1.1

Charge a Connected Device USB-C PD port connects to wall charger to power and charge the

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-C PD charging port supports power input up to 20V 3A (60W)
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power.
- Compact and easy to carry in a pocket, purse or laptop bag
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port

Package Includes

- U460-002-2AM-C USB 3.1 Gen 1 USB-C Portable Hub/Adapter
- Owner's manual



connected PD Charging-compliant USB-C/Thunderbolt 3 device Supports power input up to 20V 3A (60W)
Access Memory Card Files Card reader supports MicroSD, SD, SDHC, SDXC and MMC memory cards for convenient access to photos, videos and other data
Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

OVERVIEW	
UPC Code	037332193780
OUTPUT	
Charging Ports / Amps	1.5A; 3A
Charging Watts	60
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (1.2 Port)	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.90 x 4.00 x 5.60
Shipping Weight (lbs.)	0.30
Unit Dimensions (hwd / in.)	0.43 x 3.7 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.1
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)



Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	6.8 BTU/Hr
Power Consumption (Watts)	2
Power Provided to Connected Device(s)	5V 1.5A (7.5W) Output BC 1.2 USB port, Up to 20V 3A (60W) Input (USB-C)
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
Side B - Connector 3	MICRO SD (FEMALE)
Side B - Connector 4	SD (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
USB Power Delivery (PD) Charging Support	Yes
Technology	USB 3.1 (Gen 1); USB; PD Charging
SD Card Specification	SD; Micro SD
USB Power Delivery (PD) Charging Specification	2.0
CERTIFICATIONS	
Certifications	Tested to CE, FCC, IC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>