

## 2-Bay USB 3.0 SATA Hard Drive Docking Station with Erase Function, 2.5 and 3.5 in. HDD and SSD

MODEL NUMBER: U339-E02



Connects 2 SATA hard drives to your laptop or computer's USB port for extra storage, one-touch drive formatting and fast data transfer.

### Features

#### Connect 2 SATA External Hard Drives to Your Computer's USB Port for Extra Storage

When the hard drive on your laptop is not large enough to hold all your photos, videos, music and documents, Tripp Lite's U339-E02 is the solution. This dependable docking station allows you to connect two SATA HDD or SSD drives to any device with a USB port, including MacBooks, Ultrabooks and Chromebooks. It supports 2.5-inch SATA III, II and I drives up to 2 TB, 3.5-inch drives up to 14 TB, and will support higher capacities as they become available.

#### Transfers Data at Fast USB 3.0 Speeds with UASP Support

This dock supports USB 3.0 data transfer rates up to 5 Gbps, which is 10 times the speed of USB 2.0, to give you more data storage, retrieval and backup capacity. It reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller. The U339-E02 is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Clears the Content of 2 SATA Drives at the Same Time

An Offline Erase function reformats two SATA hard drives simultaneously at the touch of a button. A red LED blinks to indicate the Erase function is being performed. Four blue LEDs indicate progress, letting you know at a glance when the disks are completely erased. Note: The Erase function will not work if the U339-E02 is connected to a computer or any other source via USB cable.

#### Just Plug and Play for Immediate Use Right Out of the Package

No software or drivers are required. The U339-E02 is compatible with all USB-enabled operating systems, including Windows, Mac and Linux. The included power supply with six-foot cord and NEMA 1-15P plug connects to a convenient wall outlet, PDU or UPS system.

### Highlights

- Connects dual SATA HDD (hard disk drives) or SSD (solid state drives) to your computer
- Supports 2.5 in. SATA III, II and I drives up to 2 TB; 3.5 in. SATA drives up to 14 TB
- Supports USB 3.0 speeds up to 5 Gbps to ensure fast data transfers
- Reads data up to 70% faster when connected to UASP host controller
- One-touch erase feature formats 2 hard drives with no computer connection needed

### Applications

- Archive backup data quickly to an external SATA drive
- Transfer video, photos and other data from one SATA drive to another
- Erase up to 2 SATA drives simultaneously

### System Requirements

- 2.5 in. or 3.5 in. SATA HDD and/or SSD
- Device with USB-A port (USB 3.0 required to achieve USB 3.0 data transfer speeds)
- Windows, Mac or Linux operating system

### Package Includes

- U339-E02 2-Bay USB 3.0 SATA Hard Drive Docking Station
- External power supply with NEMA 1-15P plug (Input:



100–240V, 50/60 Hz, 1.5A;

Output: 12V 3A)

- USB 3.0 A-to-B cable, 3 ft.
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332248176
INPUT	
Voltage Compatibility (VAC)	100; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V~50/60Hz, 1.5A
External Power Supply Output Specs (V / A)	12V/3A
External Power Supply Cord Length (ft.)	6.4
External Power Supply Cord Length (m.)	1.95
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Certifications	FCC; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Read, Write, Power); Blue (Erase)
PHYSICAL	
Color	Black
Material of Construction	ABS
Unit Dimensions (hwd / in.)	2.44 x 15.33 x 4.38
Unit Packaging Type	Box
Unit Weight (kg)	0.41
Unit Weight (lbs.)	0.9
ENVIRONMENTAL	
Operating Temperature Range	50 to 122°F (10 to 50°C)
Storage Temperature Range	32 to 149°F (0 to 65°C)



Relative Humidity	10% to 80% RH, Non-Condensing
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	USB 3.0 B (FEMALE)
Side B - Connector 1	(2) 22 PIN SATA + POWER (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
Technology	SATA/eSATA; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
SATA Version	SATA I (1.5 Gbps); SATA II (3 Gbps); SATA III (6 Gbps)
<b>CERTIFICATIONS</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>