


## Cat8 25G/40G Certified Snagless Shielded S/FTP Ethernet Cable (RJ45 M/M), PoE, White, 10 ft.

MODEL NUMBER: N272-010-WH



Shielded Cat8 cable connects 25G/40G equipment, such as webcams and VoIP phones, in your high-speed 40GBase-T network.

### Features

#### High-Speed Cat8 F/STP Patch Cable Up to 4 Times Faster Than Cat6a

This certified Cat8 cable transmits 40 Gbps data, voice and audio/video through high-speed 40G equipment, including network switches, modems, routers, adapters, hubs and patch panels. Not only is the 40 Gbps data transfer speed four times that of Cat6a cable, but this Cat8 cable supports bandwidth up to 2 GHz (2000 MHz) for carrying information and streaming video with no lag.

#### Supports Power over Ethernet (PoE) to Cut Down on Power Supplies

Because this Cat8 shielded cable supports PoE, it can supply the power to operate compatible PoE devices, such as security cameras, VoIP telephones, point-of-sale kiosks and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. You can also install PoE devices in locations distant from power outlets, such as high on walls, ceilings or poles.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

EMI (electromagnetic interference) and RFI (radio frequency interference) line noise is a common cause of performance problems. The 22 AWG S/FTP (shielded foiled twisted pair) cable's foil shielding blocks disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer. Near-end crosstalk (NEXT) levels are practically eliminated, so you don't have to worry about keeping your cables separated in crowded pathways or spend valuable time on field testing.

#### Snagless RJ45 Male Connectors Add Extra Protection During Installation

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. Integral strain relief provides extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

#### Color-Coded to Avoid Misidentification That Can Cause Costly Downtime

This Cat8 patch cable features a durable white PVC jacket. The color-coding allows easy, fast identification in a crowded rack, patch panel or workstation, preventing the cable from becoming accidentally disconnected.

### Highlights

- Certified Cat8 S/FTP patch cord rated for 40 Gbps networks—4x faster than Cat6a
- Supports PoE to save you expense and effort of powering PoE devices individually
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Snagless RJ45 connectors prevent tabs from being damaged during installation
- Color-coded white for fast, easy identification in a crowded rack or workstation

### Applications

- Connect 40GBase-T networks or digital signage in your office, home, school or retail business' high-density server room or data center
- Deliver power to PoE devices, including security cameras and VoIP phones, mounted in areas that are difficult to reach or have no electrical outlets
- Provide universal connectivity for LAN network components, such as enterprise Ethernet switches, cloud servers, modems, routers, surveillance equipment and point-of-sale kiosks

### Package Includes

- N272-010-WH Cat8 25G/40G-Certified Snagless S/FTP



Network Patch Cable (RJ45  
M/M), White, 10 ft.

## Specifications

OVERVIEW	
UPC Code	037332249760
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Cable Length (cm)	304.8
PHYSICAL	
Cable Jacket Rating	CM
Cable Outer Diameter (OD)	8.0MM
Cable Shielding	S/FTP
Color	White
Crossover Wiring	No
Material of Construction	PVC
Snagless Connector	Yes
Wire Type	Solid
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	-5 to 140 F (-15 to 60 C)
Relative Humidity	0% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
Network Speed	40 Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Contact Plating	Gold



<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	PoE; Cat8
<b>CERTIFICATIONS</b>	
Certifications	Tested to RoHs, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>