



Cat6a 10G Snagless Molded Slim UTP Ethernet Cable (RJ45 M/M), Black, 25 ft.

MODEL NUMBER: N261-S25-BK









Slim Cat6a cable connects critical components, such as servers, switches, routers and hubs, in highdensity 10G Ethernet networks.

Features

Cat6a Cable Ideal for Your High-Density 10 Gigabit Ethernet Network

This Cat6a 10G Ethernet cable with RJ45 connectors is recommended for connecting network components like printers, computers, copiers, routers, servers, modems, hubs and switches in high-density data centers and network closets. Designed for fast transmission and excellent signal quality, this 25-foot black cable ensures peak performance throughout your LAN.

Special Slim Design for Better Airflow and Easier Installation

This Cat6a UTP patch cord is more than 38% smaller in diameter than standard Cat6a cable. This increases airflow in tight spaces, which helps keep your equipment cool and properly functioning. It also cuts down on clutter in crowded racks and patch panels, and makes the cable easier to install around corners and through cable management panels.

Snagless RJ45 Male Connectors Add Extra Protection

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. The ends feature 50-micron gold plating to help ensure the most accurate signal transfer possible, improving near-end crosstalk (NeXT) performance to 650 MHz.

Premium Construction for Superior Performance

Manufactured from 28 AWG copper wire, the four-pair stranded cable is rated for speeds up to 10 Gbps. Integral strain relief gives the unshielded cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

Highlights

- Cat6a UTP Ethernet patch cable rated for high-speed 10 Gbps communications
- Over 38% slimmer than standard Cat6a cables to increase airflow in full racks
- Easy to route around corners and through crowded cable management panels
- Snagless RJ45 connectors prevent tabs from being damaged during installation

Applications

- Connect a computer and its peripherals to a home or office
 10G network
- Connect switches, modems and servers in a high-density data center, telecom room or network closet
- Replace standard-diameter cables in crowded patch panel installations to improve airflow

Package Includes

 N261-S25-BK Cat6a 10G Snagless Molded Slim UTP Network Patch Cable (M/M), Black, 25 ft.

Specifications

OVERVIEW	
UPC Code	037332251800
INPUT	





Cable Length (ft.)	25
Cable Length (m)	7.6
Cable Length (in.)	300
Cable Length (cm)	762
PHYSICAL	
	CM
Cable Jacket Rating	CM
Cable Outer Diameter (OD)	3.8mm
Cable Shielding	UTP
Color	Black
Crossover Wiring	No
Material of Construction	PVC
Snagless Connector	Yes
Wire Gauge (AWG)	28
Wire Type	Stranded
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Relative Humidity	0% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
Network Speed	10Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Technology	Cat6a
CERTIFICATIONS	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies