

7-Port USB 3.0 / USB 2.0 Combo Hub - USB Charging, 2 USB 3.0 & 5 USB 2.0 Ports

MODEL NUMBER: U360-007C-2X3



Adds 7 USB ports to your computer, laptop, MacBook or Chromebook for connecting hard drives, tablets, webcams and other USB devices.

Features

USB 3.0/2.0 Hub Adds 7 USB Devices to Your Computer, MacBook or Chromebook

This 7-port USB 3.0 hub connects directly to the USB-A port on your computer, laptop, MacBook, Ultrabook or Chromebook. It allows you to use as many as seven USB devices, such as flash drives, external hard drives, printers, barcode scanners, webcams, keyboards/mice and power meters, all at the same time.

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers

Two USB 3.0 ports support data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0 and recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. Five USB 2.0 ports transfer data at speeds up to 480 Mbps. All seven ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Charge a Device Even When Your Computer or Laptop Is Not in Use

The first USB 3.0 port, which is labeled with a charge symbol, can charge a mobile device, such as a smartphone or tablet, when the source device is in Suspend mode only. A blue LED indicates the hub is receiving sufficient power to support all connected devices.

Plug-and-Play Hub Comes Ready to Connect Right Away

The U360-007C-2X3 works with Windows and Mac computers and requires no software or drivers to download and install. The included external power supply comes with four international plug adapters that ensure you can use the hub almost anywhere. Most of the time, the hub will receive plenty of power from your computer or laptop. The included power supply should only be necessary when connecting high-current, power-hungry USB peripherals.

Sleek and Slim Housing Designed for Everyday Workspace Use or Connecting on the Go

The compact unit is designed for convenient positioning within your reach, making USB ports accessible while not taking up much workspace. It is slim enough to pack in your pocket, purse or laptop bag for use in a hotel, conference room or airport.

Highlights

- Turns your computer or laptop into a mini workstation with 7 extra USB ports
- USB 3.0 ports support SuperSpeed rates up to 5 Gbps to ensure fast data transfers
- Charging port charges mobile device when your computer/laptop is in Suspend mode
- Slim aluminum hub fits easily in your backpack or laptop bag for connecting on the go
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 7 USB peripherals, such as an external hard drive, MP3 player, power meter and printer, to your MacBook or Chromebook
- Transfer files quickly to and from a USB thumb drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Download photos from a digital camera

System Requirements

- Compatible with all USB-enabled operating systems (USB 3.0 port needed to



achieve USB 3.0 speeds)

Package Includes

- U360-007C-2X3 7-Port USB 3.0 / USB 2.0 Combo Hub
- USB-A to USB Micro-B 3.0 cable, 3 ft.
- External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 5V 4A)
- (4) International plug adapters (North America, U.K., Europe, Australia)

Specifications

| OVERVIEW | |
|---|--|
| UPC Code | 037332242082 |
| INPUT | |
| Voltage Compatibility (VAC) | 100; 110; 120; 125; 127; 200; 208; 220; 230; 240 |
| External Power Supply Input Specs (V / Hz / A) | 100-240V~50/60HZ, 0.6A |
| External Power Supply Output Specs (V / A) | 5V/3A |
| External Power Supply Cord Length (ft.) | 4.9 |
| External Power Supply DC Barrel Connector Specs | OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve |
| External Power Supply Plug(s) | AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America |
| External Power Supply Certifications | CCC; CE; GS; PSE; TUV; UL; cUL |
| Bus Powered | Yes |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | POWER LED (BLUE) |
| PHYSICAL | |
| Color | White |
| Material of Construction | ABS |



| | |
|---------------------------------------|---|
| Unit Dimensions (hwd / in.) | 0.63 x 6.5 x 1.28 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.06 |
| Unit Weight (lbs.) | 0.13 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113°F (0 to 45°C) |
| Storage Temperature Range | 23 to 158°F (-5 to 70°C) |
| Relative Humidity | 5% to 85% RH, Non-Condensing |
| Power Provided to Connected Device(s) | 5V 0.9A (4.5W) when bus powered |
| CONNECTIONS | |
| Ports | 7 |
| Side A - Connector 1 | (2) USB 3.0 A (FEMALE) |
| Side A - Connector 2 | (5) USB A (FEMALE) |
| Side B - Connector 1 | USB 3.0 MICRO-B (FEMALE) |
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 2.0 (up to 480 Mbps); USB 3.0 (up to 5 Gbps) |
| Driver Required | No |
| Technology | USB 2.0 (High Speed); USB 3.0 (SuperSpeed); USB 3.1 (Gen 1) |
| CERTIFICATIONS | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>