


NOTE:

- 1.OPEN/SHORT/INTERMITTENCE:100%.
- 2.CONDUCTIVE RESISTANCE:2Ω (MAX)
- 3.RoHS & REACH Compliant

PIN OUT



SHELL ——— SHELL

⑥	THUMB SCREW	NICKEL PLATED#4-40*15	2	PCS
⑤	THUMB NUT	NICKEL PLATED#4-40	2	PCS
④	MOLDED	45P BLACK PVC		G
③	MOLDED	LD-PE		G
②	CONNECTOR	USB2.0 A FEMALE NICKEL PLATED	2	PCS
①	CABLE	7/0.127TC*1P+7/0.20TC*2C+AD(1/0.254BC)B(64#/0.12AL-MG) OD:4.8±0.2MM	L	MM
NO.	MATERIAL	DESCRIPTION	QTY.	UNIT

Ltemref	Quantity	Title/Name,designation,material,dimension etc	Article No./Reference		
Designed by ALVIN	Checked by HELEN	Approved by - date 11-02-2020	File name	Date 11-02-2020	Scale FREE
ANGLE:			USB2.0 Panel Mount A Female/Normal A Female 1.0M		
UNIT:MM			AV28704 PSG3299	Edition 1	Sheet 1/1